



878

878

HALF-WAVE HIGH-VACUUM RECTIFIER

FOR USE WITH CATHODE-RAY TUBES

Filament	Tungsten	
Voltage	2.5	a-c volts
Current	5.0	amp.
Overall Length		7" to 7-5/8"
Maximum Diameter		1-13/16"
Bulb		T-14
Cap		Medium Metal Skirted
Base		Medium 4-Pin

Operating Conditions:

Filament Voltage	2.5	a-c volts
A-C Plate Voltage (RMS)	7100 max.	volts
Peak Inverse Voltage	20000 max.	volts
D-C Output Current (Continuous)	5 max.	ma.

The 878 is for use in suitable rectifying devices to supply the d-c voltage requirements of cathode-ray tubes.

It is important that the filament transformer secondary be insulated to withstand the maximum peak inverse voltage encountered in the installation.

The *maximum peak plate current* of the 878 is limited by the available emission from the filament. In normal operation, the peak current is practically independent of the size of input filter condenser and is approximately 20 milliamperes.

Filter requirements are ordinarily met by the use of a 0.5 to 2.0 μ f condenser shunted across the bleeder circuit. The shunt condenser should have a rating sufficient to withstand the instantaneous peak value of the a-c input voltage. If this filtering is inadequate for a definite application, a two-section filter is recommended.


In a *voltage-doubler circuit*, two 878's may be operated to deliver approximately twice the voltage obtainable from a half-wave rectifier circuit for the same a-c input voltage. However, a separate filament-supply winding is required for each tube.

878




878

HALF-WAVE HIGH-VACUUM RECTIFIER



TUBE SYMBOL & TOP VIEW
OF
SOCKET CONNECTIONS



JAN. 15, 1936

RCA RADOTRON DIVISION
RCA MANUFACTURING COMPANY, INC.

DATA